

Rittal – The System.

Faster – better – everywhere.



SV 9690.030 Energy storage frame

State: 10/06/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9690.030 - Energy storage frame VX ESS

Enclosure frame with roof plate and flexible interior fit-out. Ideal for efficient and modular energy storage installation.

Features

| | |
|-------------------------------|---|
| Model No. | SV 9690.030 |
| Material | Enclosure frame: Sheet steel, 1.5 mm Mounting angles: Sheet steel, 2 mm Cross-member with mounting angle: Sheet steel, 3 mm |
| Surface finish | Enclosure frame: Dipcoat-primed Mounting angles: Zinc-plated Cross-member with mounting bracket: Zinc-plated |
| Colour | RAL 7035 |
| Supply includes | Enclosure frame |
| Dimensions | Width: 600 mm Height: 2,000 mm Depth: 600 mm |
| Packs of | 1 pc(s). |
| Net weight | 42 kg |
| Gross weight | 42.5 kg |
| PCF per pack (cradle-to-gate) | 106.89 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |
| Product description | VX ESS energy storage frame WxHxD: 600x2000x600 mm, with interior fit-out |