Rittal – The System.

Faster – better – everywhere.



# SV 9635.320

# Component adaptor

State: 04/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SV 9635.320 - Component adaptor 3-pole

For assembly of switchgear and protective gear.

## Features

| | |
|---|---|
| Model No. | SV 9635.320 |
| Design | Basic |
| Function principle | For mechanical attachment and direct contacting of electrical equipment on the board |
| Material | Polyamide<br>Fire protection corresponding to UL 94 |
| Colour | RAL 7035 |
| Note | The technical data may vary for UL applications |
| Rated current max. | 32 A |
| Rated operating voltage | 600 V (DC), 3~<br>690 V (AC), 3~ |
| Number of poles | 3-pole |
| Electrical ratings UL | Rated operating voltage (max.) UL: 600 V AC |
| Connection cables (AWG) | AWG 10 |
| Length of connection cable | 100 mm |
| Support rails Qty/height | 1 / 10 mm |
| Support rail type | static |
| Dimensions | Width: 45 mm<br>Height: 160 mm<br>Depth: 34.5 mm |
| Packs of | 4 pc(s). |
| Net weight | 0.44 kg |
| Gross weight | 0.513 kg |
| Copper weight (kg per piece) | 0.044 |

© Rittal 2026

# Features

| | |
|---|---|
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Component adaptor (Basic), 32 A, 690 V (AC), 600 V (DC), 3-pole, connection cable AWG 10 (L: 100 mm), WH: 45x160 mm |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |