Rittal – The System.

Faster – better – everywhere.



# CS 9781.686

# CS Toptec, bayable

State: 07/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# CS 9781.686 - CS Toptec, bayable

Bayable, twin-walled outdoor enclosure with 100 mm base/plinth, door, rear panel and seamlessly bayable weather canopy. The entire enclosure frame is available for efficient, flexible interior installation.





## Features

| | |
|---|---|
| Model No. | CS 9781.686 |
| Design | for baying<br>Without cut-out |
| Material | Enclosure frame: Stainless steel 1.4301 (AISI 304)<br>Enclosure panels and base/plinth trim: Aluminium, AlMg3<br>Rain canopy: Aluminium |
| Surface finish | Powder-coated<br>UV-resistant pure polyester |
| Colour | RAL 7035 |
| Supply includes | Bayable, twin-walled outdoor enclosure<br>Enclosure frame with 25 mm system punchings in the roof and base frame plus vertical sections with two mounting levels<br>Front door with door stay, swing lever handle and profile half-cylinder, lock BJ 20027<br>Rear panel<br>Rain canopy<br>Base/plinth with screw-fastened gland plates and screw-fastened trim panels front and rear<br>Door hinged on the right, may be swapped to the left |

© Rittal 2026

# Features

| | |
|---|---|
| Dimensions | Width: 600 mm<br>Height: 1,800 mm<br>Depth: 600 mm |
| Dimensions | Overall height: 1,945 mm<br>Rain canopy height: 45 mm<br>Height base/plinth: 100 mm |
| Number of doors | 1 |
| Lock | Lock version: 4-point locking<br>Number of locks: 1<br>Lock insert: BJ20027 |
| Gland plate | Size: 2<br>Qty.: 2 |
| Type rating to 508A | Type 1<br>Type 3R<br>Type 12 |
| IP protection category to IEC 60 529 | IP 55 |
| Protection category NEMA | NEMA 3R<br>NEMA 12 |
| IK Code | IK10 |
| Note | All enclosure panels are doubled and earthed (external wall onto internal wall)<br>When assembling a free-standing enclosure, bayable side panels for CS Toptec are required |
| Packs of | 1 pc(s). |
| Net weight | 60 kg |
| Gross weight | 70 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |

# Features

| | |
|---|---|
| Product description | CS Toptec, bayable, WxHxD: 600x1800x600 mm, overall height incl. 100 mm base/plinth and 45 mm rain canopy: 1945 mm |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |

# Tender text

Outdoor enclosure Toptec, bayable

Toptec Outdoor Housing Single door, double walled
Outdoor housing with 100 mm transport base/plinth and
Rain canopy projecting on all sides.
Rear wall and door completely doubled on the outside,
the complete TS 8 frame stands for the interior fittings
at your disposal.
Double-walled outdoor housing, completely pre-assembled
TS 8 frame with 25 mm system perforation in roof and
Base frame and vertical profiles with 2 fixing levels
Front door with door stop, lever handle and
Profile half cylinder, locking BJ20027
Rear panel
Rain cover
Base with bolted flange plates and
screwed front and rear panels
Door:
with 4-point lock and lever handle
with C83N profile half cylinder with lock BJ20027
Flat parts:
Roof, door, rear wall, floor panels
(2 flange plates, size: 340x150 mm)
included in delivery.

© Rittal 2026

All flat parts doubled and earthed
(outer wall to inner wall).
Accessories: Side panels, Baying-Kit, AX gland plates
Adapter rail for VX compatibility, Swing frame VX
Material:
Housing frame: stainless steel 1.4301 (AISI 304)
Flat parts and plinth panels: Aluminium, AlMg3
Rain cover: aluminium
Surface finish:
Powder-coated
UV-resistant pure polyester
External surfaces in RAL 7035 structure Outdoor
powder-coated.
Protection class according to IEC 60 529: IP 55
Impact protection according to IEC 62 262: IK10
Dimensions (W x H x D): 600x1800x600 mm