Rittal – The System.

Faster – better – everywhere.





KL 1504.510 Terminal boxes KL

State: 07/11/2025 (Source: rittal.com/gr-en)



KL 1504.510 - Terminal boxes KL without gland plate

Spray-finished enclosure with sheet steel cover, without gland plate Protection category IP 66.

Features

| Model No. | KL 1504.510 |
|-----------------------------------|---|
| Material | Enclosure: Sheet steel Cover: Sheet steel, all-round foamed-in PU seal |
| Surface finish | Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint |
| Colour | RAL 7035 |
| Supply includes | Enclosure with cover Quick-release fastener including plastic bushes |
| Protection category NEMA | NEMA 4 |
| Protection category to IEC 60 529 | IP 66 |
| IK Code | IK08 |
| Dimensions | Width: 400 mm Height: 200 mm Depth: 120 mm |
| Material thickness - cover | 1.25 mm |
| Material thickness - enclosure | 1.25 mm |
| Basic material | Sheet steel |
| Packs of | 1 pc(s). |
| Net weight | 3.311 |
| Gross weight | 3.6 |
| Customs tariff number | 85389099 |
| EAN | 4028177251168 |
| E-Number Sweden | E3404666 |
| ECLASS 8.0 | 27180101 |
| | |

© Rittal 2025

Approvals

| Approvals | Bureau Veritas |
|--------------|------------------------------|
| | DNV-GL |
| | Lloyds Register of Shipping |
| | UL + C-UL (listed) |
| Explanations | Manufacturer's declaration |
| | Declaration of conformity UK |

Tender text

Terminal box without gland plate (120 mm deep), protection cat. IP 66 Enclosure:

sturdy sheet steel construction, folded and welded from a single piece, with all-round protection channel on the cover aperture, rear panel with recessed holes for wall mounting brackets, cover of sheet steel, sealed, with a highly elastic, foamed-in special seal, facilities for connecting PE conductors in the cover and box, profile strips on both internal sides with mounting holes. Special plastic bush guards against accidental loss of the cover screws and provides screwdriver guidance.

Accessories:

quick-release fastener, cover retainer, plastic cable gland plate, cover hinges, mounting plate

Surface finish:

steel is cleaned, degreased, phosphated, electrophoretic dipcoat primed and electrostatically polyester powder-coated in textured RAL 7035 Dimensions (W x H x D): 400 x 200 x 120 mm

© Rittal 2025 3