

# Rittal – The System.

Faster – better – everywhere.



## AX 2260.965

## AX wall-mounted enclosure, 3-part

State: 09/07/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2260.965 - AX wall-mounted enclosure, 3-part With Blue e+ outlet filter

The delivery concept behind the three-part AX wall-mounted enclosures reduces complexity and enhances flexibility. The AX/VX modular system makes these enclosures suitable for a range of applications. The three-part structure ensures easy access.



## Features

|                 |                                                                                                                                                                                                                                                                                                                                                                                                |
|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.       | AX 2260.965                                                                                                                                                                                                                                                                                                                                                                                    |
| Design          | Wall-mounted enclosures IT                                                                                                                                                                                                                                                                                                                                                                     |
| Material        | Wall and hinged part: Sheet steel, 1.5 mm<br>Viewing window: Single-pane safety glass, 3 mm                                                                                                                                                                                                                                                                                                    |
| Surface finish  | Powder-coated                                                                                                                                                                                                                                                                                                                                                                                  |
| Colour          | Wall and hinged part: RAL 7035<br>Glazed door: RAL 7035/7015 (slate grey)                                                                                                                                                                                                                                                                                                                      |
| Supply includes | Wall section: Gland plate, solid, top and bottom<br>Hinged part with 25 mm pitch pattern of holes in the front and rear frame, and two 482.6 mm (19") mounting angles, front, static installation<br>Designer glazed door<br>Designer glazed door lock: Security lock 3524 E<br>Centre part lock: 3 mm double-bit<br>2 Blue e+ outlet filters 3238.300 (supplied loose)<br>Mini-comfort handle |
| Units           | 9 U                                                                                                                                                                                                                                                                                                                                                                                            |

# Features

|                                        |                                                                                                                                                                    |
|----------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Dimensions                             | Width: 600 mm<br>Height: 478 mm<br>Depth: 673 mm                                                                                                                   |
| Installation depth                     | 620 mm                                                                                                                                                             |
| Clearances                             | Clearance width: 502 mm<br>Clearance height: 417 mm                                                                                                                |
| Depth hinged part                      | 516 mm                                                                                                                                                             |
| Depth of wall section                  | 135 mm                                                                                                                                                             |
| Number of locks                        | 1                                                                                                                                                                  |
| IK Code                                | IK08                                                                                                                                                               |
| Load capacity of hinged part (static)  | 450 N                                                                                                                                                              |
| Load capacity of wall section (static) | 150 N                                                                                                                                                              |
| Basic material                         | Sheet steel                                                                                                                                                        |
| Lock                                   | Lock version: Mini-comfort handle<br>Lock insert: Security lock insert no. 3524 E                                                                                  |
| Protection category to IEC 60 529      | IP 54 in conjunction with solid gland plate top and bottom                                                                                                         |
| Customs tariff number                  | 94032080                                                                                                                                                           |
| Product description                    | AX wall-mounted enclosure, 3-part with Blue e+ outlet filter, WxHxD: 600x478x673 mm, 9 U, wall section: Solid gland plate top and bottom, with mini-comfort handle |

# Approvals

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |