

# Rittal – The System.

Faster – better – everywhere.



## SZ 2411.611

## Cable gland, polyamide

State: 22/08/2025 (Source: [rittal.com/gr-en](https://www.rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2411.611 - Cable gland, polyamide

Integrated clamping membranes ensure reliable tightening and strain relief to protect the cables.

## Features

Model No.	SZ 2411.611
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables
Material	Polyamide 6 Seal: CR/NBR
Colour	RAL 7035
IP protection category to IEC 60529	IP 68 (5 bar, 30 min)
Dimensions	Height: 30 mm
Thread	M16 x 1.5
Thread length	10 mm
Min. cable diameter	5 mm
Max. cable diameter	10 mm
Operating temperature range	-30 °C...100 °C
torque	2.5 Nm
Width across flats	22 mm
Dimensions	Thread: M16 x 1.5 Thread length: 10 mm
Type rating to UL 50E	Type 4X
Packs of	50 pc(s).
Net weight	0.5
Gross weight	0.546

# Features

Customs tariff number	39269097
EAN	4028177810006
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

# Approvals

Approvals	CSA + CSAus UR + C-UR (recognized) VDE
Explanations	Declaration of conformity Declaration of conformity UK