

# Rittal – The System.

Faster – better – everywhere.



## SK 3187.935

# Wall-mounted cooling unit Blue e+ chemical

State: 18/04/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3187.935 - Wall-mounted cooling unit Blue e+ chemical 1.6 - 5.5 kW

Energy-efficient Blue e+ wall-mounted chemical industry cooling units in output classes ranging from 1600 W to 5500 W. Thanks to a special surface finish, these units provide components with optimum protection in contaminated environments – especially in applications where the air may contain sulphuric acid aerosols.

## Features

Model No.	SK 3187.935
Design	wall-mounted chemical
Benefits	Average 75% energy savings thanks to speed-regulated components and heat pipe technology Suitable for international use thanks to its unique multi-voltage capability (without rewiring) and high operating limits Longer service life of the components inside the enclosure and the cooling unit due to component-friendly cooling Intuitive operation due to touch display and intelligent interfaces
Product modification	The cover for the connection box to protect the electrical connection to the cooling unit has not been included with the supply since the start of 2024. Covers 3355.200 and 3355.210 can be ordered as optional accessories.
Applications	Applications where the air may contain sulphuric acid aerosols (e.g. paper industry, food industry, chemical industry, electroplating and offshore operations)
Material	Sheet steel
Surface finish	Sheet metal parts and electronics: Clear varnish coating Cooling circuit with two-component PUR coating
Colour	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Integral electric condensate evaporation Assembly parts Fully wired ready for connection (plug-in terminal strip)

# Features

Options	For remote monitoring and networking of cooling units and chillers in the Blue e+ generation, please use the IoT interface (Model No. 3124.300). Increase machine availability and process reliability with remote monitoring of device data, statuses and system messages.
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 2.6 kW Cooling output L35 L35/60 Hz: 2.6 kW Cooling output L35 L50/50 Hz: 1.7 kW Cooling output L35 L50/60 Hz: 1.7 kW
Rated operating voltage	110 V - 240 V, 1~, 50 Hz/60 Hz 380 V - 480 V, 3~, 50 Hz/60 Hz
Note	Please observe the mounting instructions. By downloading the software, a contract is concluded between the contractual partner and Rittal for the free use of the software in accordance with these licence conditions. Only suitable for use in semi-outdoor areas (see instructions for description)
Note on Model No.	Tolerance: 110 V -10% (99 V) and 240 V +10% (264 V) / 380 V -10% (342 V) and 480 V +6% (509 V)
Rated power input	1.05 kW
Air throughput (unimpeded air flow)	External circuit: 1,250 m <sup>3</sup> /h Internal circuit: 1,250 m <sup>3</sup> /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.63 Refrigeration factor L35 L35 (EER) 60 Hz: 2.63
Seasonal energy efficiency ratio (SEER) 50/60 Hz	6.2
Design	wall-mounted
Dimensions	Width: 450 mm Height: 1,600 mm Depth: 294 mm
Required mounting cut-out	Cut-out width: 433 mm Cut-out height: 1,579 mm
Protection category to IEC 60 529	Internal circuit IP 55

# Features

---

Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 1.07 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 0.68 t
Temperature control	e+ controller (factory setting +35 °C)
Operating temperature range	-20 °C...60 °C
Storage temperature range	-40 °C...70 °C
Operating temperature range of refrigerant circuit (active)	3 °C...60 °C
Heat pipe operating temperature range	-20 °C...45 °C
Setting range	20 °C...50 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 0.99 kW Power consumption L35 L35/60 Hz: 0.99 kW Power consumption L35 L50/50 Hz: 0.94 kW Power consumption L35 L50/60 Hz: 0.94 kW
Permissible operating pressure (p. max.)	24 bar
Packs of	1 pc(s).
Net weight	65 kg
Gross weight	70 kg
Customs tariff number	84158200
Product description	SK Cooling unit Blue e+ chemical, wall-mounted, 2.6 kW, 110-240 V, 1~, 380-480 V, 3~, 50-60 Hz, sheet steel, WHD: 450 x 1600 x 294 mm

---

# Approvals

---

Approvals	IEC CB 30 - KC Korea
-----------	-------------------------

---

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity - F-gas regulation

Declaration of conformity UK