

Rittal – The System.

Faster – better – everywhere.



SM 2384.030 Switch housings

State: 10/07/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SM 2384.030 - Switch housings Stainless steel

Switch housing made from stainless steel 1.4301 (AISI 304) with switch cut-outs, diameter: 22.5 mm. Protection category IP 66.

Features

| | |
|-----------------------------------|---|
| Model No. | SM 2384.030 |
| Material | Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal |
| Surface finish | Enclosure and cover: Brushed, grain 240 |
| Supply includes | Enclosure with cover Quick-release fastener including plastic bushes |
| Protection category NEMA | NEMA 4X |
| Protection category to IEC 60 529 | IP 66 |
| IK Code | IK08 |
| Dimensions | Width: 220 mm Height: 100 mm Depth: 90 mm |
| Material thickness - cover | 1.25 mm |
| Material thickness - enclosure | 1.25 mm |
| Pitch pattern | 60 mm |
| Cut-outs (quantity x diameter) | 3 x 22.5 mm |
| Lock | Lock version: Quick-release fastener including plastic bushes Number of locks: 4 |
| Cable entry (quantity x diameter) | 3 |
| No. of metric knockouts | 3 |
| Basic material | Stainless steel 1.4301 (AISI 304) |
| Packs of | 1 pc(s). |
| Net weight | 1.1 kg |

Features

| | |
|-------------------------------|--|
| Gross weight | 1.226 kg |
| PCF per pack (cradle-to-gate) | 4.46 |
| Customs tariff number | 84879090 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | SM Switch housing, WHD: 220x100x90 mm, Stainless steel 1.4301, without mounting plate, 3 switch cut-outs |

Approvals

| | |
|--------------|--|
| Explanations | Declaration of conformity Declaration of conformity UK PCF-declaration |
|--------------|--|