Rittal – The System.

Faster – better – everywhere.





SK 3209.504 Air/water heat exchangers

State: 08/12/2025 (Source: rittal.com/gr-en)



SK 3209.504 - Air/water heat exchangers roof-mounted

For mounting on the roof surface. Cooling output 1.87 kW – 4 kW. Protection category IP 55 as standard. Particularly suitable for use in harsh environments. Flexible water connection options.





Features

Model No.	SK 3209.504
Design	roof-mounted
	Water-carrying parts, stainless steel (1.4571)
Product description	For use in harsh environments and temperature ranges up to +70
	°C. The air/water heat exchanger is assembled on the roof of the
	enclosure using flexible water connection options.
Colour	RAL 7035
Supply includes	Fully wired ready for connection (plug-in terminal strip)
	Drilling template
	Sealing mat
	Assembly parts
Total cooling output	L 35 W 10 at 400 l/h: 1.87 kW
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Power consumption Pel	At 50 Hz: 95 W
	At 60 Hz: 110 W
Rated current max.	At 50 Hz: 0.4 A
	At 60 Hz: 0.48 A

© Rittal 2025 2

Features

Permissible operating pressure (p. max.)	1 - 10 bar
Type of electrical connection	Plug-in terminal strip
Duty cycle	100 %
Cooling medium	Water (see Internet for specifications)
Water inlet temperature	1 °C30 °C
Water connections	½" connector sleeve G 3/8" external thread
Temperature control	e-Comfort controller (factory setting +35 °C)
Operating temperature range	1 °C70 °C
Dimensions	Width: 597 mm Height: 417 mm Depth: 475 mm
Note on Model No.	Extended delivery times.
Protection category	IP 65 available on request
Pre-fuse	Miniature circuit-breaker/fuse: 4 A
Setting range	20 °C55 °C
Protection category to IEC 60 529	IP 55
Packs of	1 pc(s).
Net weight	32.25
Gross weight	34.5
Customs tariff number	84158300
EAN	4028177429901
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

© Rittal 2025 3

Approvals

Explanations

Declaration of conformity

Tender text

Roof-mounted air/water heat exchanger

For use in tough environments. Flexible water connection options.

Total cooling output L 35 W 10, 400l/h: 1.88 kW

Rated operating voltage: 230 V, 50/60 Hz Refrigerant: Water (see specifications)

Water-carrying parts: Stainless steel (1.4571) Dimensions [W x H x D]: 597 x 417 x 475 mm Ambient temperature range: 1°C to 70°C

Setting range: 20°C to 55°C

Water inlet temperature range: 1°C to 30°C

Temperature control and monitoring: Comfort controller

with two floating fault signal outlets and door limit

switch connection (factory setting +35°C) Type of connection: Plug-in terminal strip Protection category to IEC 60 529: IP 55

Weight: 23.5 kg Colour: RAL 7035

© Rittal 2025 4