

# Rittal – The System.

Faster – better – everywhere.



## SK 3239.724 Blue e+ filter fan

State: 16/01/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3239.724 - Blue e+ filter fan

Complete fan-and-filter units for tool-free installation in surfaces. Air throughput 20 – 1,160 m<sup>3</sup>/h, protection category IP 54 as standard.



## Features

|                     |  |
|---------------------|--|
| Model No.           | SK 3239.724  |
| Design              | wall-mounted   |
| Product description | Fan-and-filter units with diagonal fan technology have superior pressure stability and ensure a more constant air throughput. The diagonal direction of outflow ensures more even heat dissipation from the enclosure.   |
| Benefits            | <ul style="list-style-type: none"><li>Maximum air throughput via pleated filter included in the delivered state</li><li>Easy filter changes, thanks to a new opening mechanism on the louvred grille</li><li>Faster installation on the enclosure with optimised detent hooks</li><li>Diagonal fan technology achieves more even and constant ventilation of the enclosure, thanks to improved pressure stability</li><li>Tool-free assembly</li></ul> |
| Material            | Plastic  |
| Colour              | RAL 7035   |
| Supply includes     | Complete unit ready to install, including pleated filter   |
| Fan                 | Axial, DC motor  |

# Features

|   |  |
|---|--|
| Air throughput, unimpeded airflow (with chopped-fibre filter)             | With DC: 100 m <sup>3</sup> /h   |
| Air throughput, unimpeded airflow (with pleated filter)                   | With DC: 110 m <sup>3</sup> /h   |
| Air throughput with matching outlet filter including chopped-fibre filter | With DC: 75 m <sup>3</sup> /h  |
| Air throughput with matching outlet filter including pleated filter       | With DC: 92 m <sup>3</sup> /h  |
| Rated operating voltage   | 24 V (DC)  |
| Power consumption Pel   | With DC: 5.7 W   |
| Rated current max.  | With DC: 0.27 A  |
| Dimensions  | Width: 204 mm<br>Height: 204 mm<br>Depth: 105 mm   |
| Installation depth  | 84 mm  |
| Mounting cut-out  | Cut-out width: 177 mm<br>Cut-out height: 177 mm  |
| IP protection category to IEC 60 529                                      | IP 54 with chopped-fibre filter/pleated filter<br>IP 55 with pleated filter and absorber mat<br>IP 56 with chopped-fibre filter/pleated filter and hose-proof hood                   |
| Protection category NEMA  | Type 12 with chopped-fibre filter/pleated filter<br>Type 3, 3R, 4, 4X with chopped-fibre filter/pleated filter and hose-proof hood   |
| Pre-fuse  | Miniature circuit-breaker/fuse: 2 A  |
| Note  | With the filter fan 3237.XXX, electrical connection is made via two single wires (length approx. 300 mm) on the unit, for all other filter fans, a screwless spring terminal is used |
| Operating temperature range   | -15 °C...55 °C   |
| Storage temperature range   | -30 °C...70 °C   |
| Noise level   | With DC: 51 dB(A)  |
| Packs of  | 1 pc(s).   |

# Features

---

|                       |               |
|-----------------------|---------------|
| Net weight            | 0.78          |
| Gross weight          | 0.989         |
| Customs tariff number | 84145915      |
| EAN                   | 4028177998179 |
| ETIM 9                | EC000320      |
| ETIM 8                | EC000320      |
| ECLASS 8.0            | 27180716      |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | 30 - KC Korea<br>UL + C-UL - FTTA<br>UR + C-UR (recognized) |
| Explanations | Declaration of conformity                                   |