

Rittal – The System.

Faster – better – everywhere.



SK 3305.500

TopTherm wall-mounted cooling unit Blue e

State: 20/06/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3305.500 - TopTherm wall-mounted cooling unit Blue e 0.3 - 4 kW

Energy-efficient Blue e wall-mounted cooling units in the output categories 300 W to 4000 W and with integral electrical condensate evaporator (from 1000 W). Available in the special formats "horizontal" and "flat".

Features

Model No.	SK 3305.500
Design	wall-mounted
Product description	Energy-efficient Blue e wall-mounted cooling units in the output categories 300 W to 4000 W and with integral electrical condensate evaporator (from 1000 W).
Benefits	May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller
Material	Sheet steel
Colour	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Fully wired ready for connection (plug-in terminal strip) Drilling template Assembly parts Integral electric condensate evaporation
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 1.6 kW Cooling output L35 L35/60 Hz: 1.73 kW Cooling output L35 L50/50 Hz: 1.18 kW Cooling output L35 L50/60 Hz: 1.26 kW
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 6.1 A At 60 Hz: 6.5 A
Start-up current max.	At 50 Hz: 12 A At 60 Hz: 14 A

Features

Air throughput (unimpeded air flow)	External circuit: 805 m ³ /h Internal circuit: 585 m ³ /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 1.83 Refrigeration factor L35 L35 (EER) 60 Hz: 1.79
Design	wall-mounted
Dimensions	Width: 400 mm Height: 950 mm Depth: 260 mm
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54
Protection category NEMA	UL Type 12
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.61 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 0.38 t
Temperature control	e-Comfort controller (factory setting +35 °C)
Operating temperature range	10 °C...55 °C
Storage temperature range	-40 °C...70 °C
Setting range	20 °C...55 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 0.87 kW Power consumption L35 L35/60 Hz: 0.96 kW Power consumption L35 L50/50 Hz: 0.91 kW Power consumption L35 L50/60 Hz: 1 kW
Permissible operating pressure (p. max.)	28 bar
Pre-fuse	Miniature circuit-breaker/fuse: 16 A
Packs of	1 pc(s).
Net weight	39.75 kg
Gross weight	42 kg
Customs tariff number	84158200
ETIM 9	EC000855

Features

ETIM 8	EC000855
ECLASS 8.0	27180704
Product description	SK cooling unit Blue e, wall-mounted, 1.6 kW, 230 V, 1~, 50/60 Hz, Sheet steel, WHD: 400 x 950 x 260 mm

Approvals

Approvals	30 - KC Korea UL + C-UL (listed) UL + C-UL - FTFA
Explanations	Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK
