

Rittal – The System.

Faster – better – everywhere.



SK 3311.011

Fan module

State: 10/09/2025 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3311.011 - Fan module for LCP Rack/Inline CW

Increased cooling output. Additionally redundancy can be achieved or the electric power consumption can be reduced.



Features

Model No.	SK 3311.011
Product description	To increase the cooling output, individual fan modules may be retro-fitted into the LCPs. Additional integration can also achieve redundancy or reduce the electric power consumption of the LCPs.
Benefits	May be connected with the system operational Tool-free replacement of the fan modules
Function principle	Installing fan modules in an LCP increases the air throughput and hence the cooling output of the chosen variant. With an adequate cooling output, fan modules may be added to create redundancy. Retro-fitting additional fans over and above the required volumetric air flow allows you to reduce the electrical energy consumption, since the fans then operate at a lower speed. At the same time, the noise level of the unit will be significantly reduced.
Colour	RAL 9005
Supply includes	1 fan unit EC fan Fully wired ready for connection Assembly parts

Features

Note	<p>The LCP SK 3311.130/.230/.530 (max. 30 kW) is supplied with one fan module as standard.</p> <p>To achieve the max. cooling output of 30 kW, the customer/service needs to install two additional fan modules.</p> <p>The LCP SK 3311.260/.560 (max. 55 kW) is supplied with four fan modules as standard.</p> <p>To achieve the max. cooling output of 55 kW, the customer/service needs to install two additional fan modules.</p> <p>The LCP SK 3311.540 (max. 30 kW) is supplied with two fan modules as standard.</p> <p>To achieve the max. cooling output of 30 kW, the customer/service needs to install two additional fan modules.</p>
Packs of	1 pc(s).
Net weight	6.851
Gross weight	7.212
Customs tariff number	84145915
EAN	4028177688117
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

Approvals

Explanations	<p>Declaration of conformity</p> <p>Declaration of conformity UK</p>
--------------	--