



AS 4050.437 - Support rail cutter MC3

Manual profile cutter for cutting C rails 30/15 and support rails TS 35/7.5 and TS 35/15 to length, burr-free. The desired rail length can be set precisely and reproducibly using the ruler (mm/inch) and the adjustable end stop. For mounting on the workbench.



Features

Model No.	AS 4050.437
Product description	Manual profile cutter for cutting C rails 30/15 and support rails TS 35/7.5 and TS 35/15 to length, burr-free. The desired rail length is set precisely and reproducibly using the ruler (mm/inch) and the adjustable end stop. For mounting on the workbench.
Benefits	<p>Inexpensive manual cutting of mounting angles and support rails</p> <p>Easier to cut mounting angles and support rails to the correct length than sawing by hand</p> <p>Burr-free cutting to length with eccentric lever, no major force required</p> <p>Low-maintenance and with a long service life</p>
Support area	<p>Width: 1,343 mm</p> <p>Height: 1,162 mm</p> <p>Depth: 312 mm</p>
Machinable material	<p>Sheet steel</p> <p>Aluminium</p> <p>Copper</p>
Packs of	1 pc(s).
Net weight	15 kg
Gross weight	16.15 kg
Customs tariff number	73269098

Features

ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890
Product description	For cutting iron, copper and aluminium up to 1.2 mm thickness, plastic up to max. 2.0 mm thickness, cutting width 2.7 mm