

Rittal – The System.

Faster – better – everywhere.



SV 3433.010

Bus-mounting fuse base

State: 31/08/2025 (Source: [rittal.com/gr-en](https://www.rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3433.010 - Bus-mounting fuse base

3-pole, for 60 mm bar centre distance.

Features

| | |
|---|---|
| Model No. | SV 3433.010 |
| Material | Bus-mounting fuse base: Fibreglass-reinforced, thermoplastic polyester (PBT) Contact hazard protection: Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Note | Wire end ferrules should be used with fine wire conductors |
| For bar systems with centre-to-centre spacing | 60 mm |
| Type of electrical connection | Box terminal |
| Fuse inserts | D III-E 33 (adaptor screw) |
| Rated insulation voltage | 690 V |
| Rated current max. | 63 A |
| Rated operating voltage | 690 V (DC) 690 V, 3~ |
| Note | For the use of fuse inserts to EN 60 269-3 (DIN VDE 0636-3) |
| Dimensions | Width: 57 mm Height: 209 mm |
| Connection of round conductors | 1.5 - 25 mm ² |
| To fit busbars | Height: 5, 10 mm |
| Number of poles | 3-pole |
| Rated operating voltage (L1 + L2) | 690 V (DC) |
| Rated operating voltage (L1 + L3) | 690 V (DC) |
| Packs of | 10 pc(s). |

Features

| | |
|------------------------------|---------------|
| Net weight | 3 |
| Gross weight | 3.18 |
| Copper weight (kg per piece) | 0.071 |
| Customs tariff number | 85369095 |
| EAN | 4028177674998 |
| ETIM 9 | EC001644 |
| ETIM 8 | EC001644 |
| ECLASS 8.0 | 27142120 |

Approvals

| | |
|--------------|--|
| Approvals | ABS DNV-GL Lloyds Register of Shipping |
| Explanations | Declaration of conformity |