

Rittal – The System.

Faster – better – everywhere.



SV 3451.500 Conductor connection clamp

State: 05/04/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3451.500 - Conductor connection clamp

For connecting round conductors and laminated copper bars.

Features

| | |
|---|--|
| Model No. | SV 3451.500 |
| Product description | For connecting round conductors and laminated copper bars. |
| Material | Sheet steel |
| Surface finish | Zinc-plated, passivated |
| Clamping area for laminated copper bars (W x H) | 8 x 8 mm |
| Note | Wire end ferrules should be used with fine wire conductors |
| Connection of round conductors | 2.5 - 16 mm ² |
| For bar thickness | 5 mm |
| Packs of | 15 pc(s). |
| Net weight | 0.375 kg |
| Gross weight | 0.44 kg |
| PCF per pack (cradle-to-gate) | 1.6 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 85369010 |
| ETIM 9 | EC000001 |
| ETIM 8 | EC000001 |
| ECLASS 8.0 | 27141146 |
| Product description | SV Conductor connection clamp, 2,5-16 mm ² , clamping area WH: 8x8 mm, for bar thickness 5 mm |

Approvals

| | |
|--------------|---|
| Approvals | UR + C-UR (recognized) |
| Explanations | Declaration of conformity Declaration of conformity UK |

Tender text

SV conductor connection clamps
for E-CU busbars and Rittal PLS.

For bar thickness: 5 mm

Connection of round conductors: 2.5 - 16 mm²

Wire end ferrules should be used with fine
wire conductors.

Clamping area: for laminated copper bars 8 x 8 mm

Tightening torque

Conductor connection clamp: 3 Nm

Material: sheet steel, zinc plated, passivated