Rittal - The System.

Faster – better – everywhere.




SV 3580.100 Busbars E-Cu


State: 24/11/2025 (Source: rittal.com/gr-en)




SV 3580.100 - Busbars E-Cu

Length: 2400 mm/bar.







Features

| Model No. | SV 3580.100 |
|------------------------------|--|
| Material | E-Cu F30 |
| Length | 2,400 mm |
| Note | May be cut individually to required length |
| Standards | DIN EN 13 601 |
| Cross-section | 12 mm x 10 mm |
| Dimensions | Length: 2,400 mm |
| Packs of | 6 pc(s). |
| Net weight | 15.48 |
| Gross weight | 15.5 |
| Copper weight (kg per piece) | 2.58 |
| Customs tariff number | 74071000 |
| EAN | 4028177219526 |
| ETIM 9 | EC001522 |
| | |

© Rittal 2025

Features

| ETIM 8 | EC001522 |
|------------|----------|
| ECLASS 8.0 | 27370303 |

Approvals

| Approvals | UL + C-UL (listed) |
|--------------|------------------------------|
| Explanations | Declaration of conformity |
| | Declaration of conformity UK |

Tender text

Busbar made from E-Cu Busbars E-Cu to DIN 13601 Technical specifications

Length: 2400 mm

Dimension: 12 x 10 mm Cross section: 120 qmm Weight: 1.068 Kg/m Electrical parameters

IEC: to 340 A UL 508: -System:

Rittal RiLine60

© Rittal 2025 3