

Rittal – The System.

Faster – better – everywhere.



SV 3584.020

CUPONAL busbars

State: 06/08/2025 (Source: [rittal.com/gr-en](https://www.rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3584.020 - CUPONAL busbars

Copper-coated aluminium busbar



Features

Model No.	SV 3584.020
Product description	Copper-coated aluminium busbars, suitable for configuring busbar systems with busbar supports 9340.000/9340.050.
Material	Aluminium Copper
Length	2,400 mm
Rated current max.	328 A
Note	The rated current is derived at 65 °C bar temperature and 35 °C ambient temperature Correction factor diagram to DIN EN 43 671 May be cut individually to required length
Standards	DIN EN 13 601
Cross-section	30 mm x 5 mm
Dimensions	Length: 2,400 mm
Packs of	6 pc(s).
Net weight	8.52
Gross weight	9
Copper weight (kg per piece)	0.52

Features

Customs tariff number	74071000
EAN	4028177686571
ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---