

Rittal – The System.

Faster – better – everywhere.



AS 4050.887

Circular thread milling cutter

State: 27/06/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.887 - Circular thread milling cutter

Milling cutter for cutting metric threads for Perforex machining centres BC and Perforex milling terminals MT.

Features

| | |
|--------------------------|---|
| Model No. | AS 4050.887 |
| Product description | Milling cutter for cutting metric threads for Perforex machining centres BC and Perforex milling terminals MT. |
| Technical specifications | Shaft diameter 12 mm Cutting diameter 10 mm Pitch 1.5 mm Flank angle 60° Cutting length 20 mm Overall length 85 mm |
| For threads | M12 - M64 |
| Standards | DIN 13-1 metric ISO thread |
| Machinable material | Steel Stainless steel Cast aluminium Plastic Copper |
| Packs of | 1 pc(s). |
| Net weight | 0.124 kg |
| Gross weight | 0.124 kg |
| Customs tariff number | 82077031 |
| ETIM 9 | EC000945 |
| ETIM 8 | EC000945 |
| ECLASS 8.0 | 36609211 |
| Product description | Circular thread milling cutter, 10x1.5, 12 mm |