### Rittal – The System.

Faster – better – everywhere.







# AS 4055.250 Hole punch, round

State: 08/11/2025 (Source: rittal.com/gr-en)



## AS 4055.250 - Hole punch, round for sheet steel

For punching round cut-outs

#### **Features**

| Model No.  | AS 4055.250  |
|--|--|
| Design   | With 3 cutting points  |
| Product description                                | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.  |
| Supply includes                                    | Female dies<br>Male dies<br>Tension screw without ball bearing   |
| Machinable material                                | Sheet steel  |
| Maximum machinable material thickness, sheet steel | 3 mm   |
| Ø punch  | 50.5 mm  |
| For threads  | M50  |
| Note   | When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel |
| Suitable for hydraulic bolt order number           | 4055.663   |
| Tension screw (Ø x L)                              | 19 x 75 mm   |
| Hydraulic tension screw Ø                          | 19 mm  |
| Packs of   | 1 pc(s).   |
| Net weight   | 0.823  |
| Gross weight                                       | 0.897  |
| Customs tariff number                              | 82073010   |
| EAN  | 4028177808348  |
| ETIM 9   | EC000156   |

© Rittal 2025

#### **Features**

| ETIM 8     | EC000156 |  |
|------------|----------|--|
| ECLASS 8.0 | 21049047 |  |

© Rittal 2025 3