

Rittal – The System.

Faster – better – everywhere.



DK 7010.501 ADO Control Unit

State: 01/10/2026 (Source: www.rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7010.501 - ADO Control Unit

Control unit for automatic opening of glazed doors VX IT for ADO with integral vent flaps.
Designed for a rack with front and rear door.

Features

Model No.	DK 7010.501
Design	ADO Control Unit
Benefits	Stand-alone operation supported
Technical specifications	1st rated voltage: 24 V (DC) 7030.060 for door control module and glazed doors VX IT for ADO, redundant to 2nd rated voltage 2nd rated voltage: 24 V (DC) 7030.060 for door control module and glazed doors VX IT for ADO 1 x temperature sensor input 3 x digital inputs: Alarm/front door flaps/rear door flaps 1 x input for reader units: Combination lock/transponder reader for local function testing of the vent flaps 2 x outputs for glazed doors VX IT for ADO with integral vent flaps, magnetic system with damper integrated into the door 2 x CAN bus CMC III: RJ45 for CAN bus cable
Applications	Enclosure monitoring in IT, industry and facility management Monitoring of enclosures, rooms and containers in the IT environment
Material	Plastic
Surface finish	Front: Smooth Enclosure: Textured
Colour	RAL 9005
Supply includes	Temperature sensor including connection cable (supplied loose) Assembly parts for mounting on surfaces
Operating temperature range	0 °C...45 °C
Ambient humidity (non-condensing)	5...95 %
Packs of	1 pc(s).

Features

CRA risk class	Default (Low Risk)
Customs tariff number	90330090
Product description	DK ADO control unit for the automatic door opening system, activation of up to 2 door kits and 2 door extension kits for LCP, WHD: 138x40x132 mm

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity