

# Rittal – The System.

Faster – better – everywhere.



## DK 7856.025 Connection cable

State: 18/06/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7856.025 - Connection cable for PSM rail

Preassembled connection cable for the Power System Module.

## Features

|                       |  |
|-----------------------|--|
| Model No.             | DK 7856.025  |
| Design                | 3-phase  |
| Connector (type)      | CEE (3P+N+PE)  |
| Rated current (max.)  | 16 A   |
| Dimensions            | Length: 3 m  |
| Sockets               | Wago X-Com   |
| Packs of              | 1 pc(s).   |
| Net weight            | 0.94 kg  |
| Gross weight          | 0.96 kg  |
| Customs tariff number | 85444290   |
| ETIM 9                | EC001576   |
| ECLASS 8.0            | 27060402   |
| Product description   | DK Connection cable, L: 3 m, 16 A, 3-phase, Wago X-Com, CEE, For PSM |

# Tender text

## Power System Module connection cable

Installation via the plug & play system:

The pre-configured connection cable with fitted AC IEC309 plug is used to supply the power system module plus busbar. A 5-pole plug-in connector strip is used to connect up to the busbar.

Another connection cable is required to supply the second redundant power circuit.

Technical specifications:

Three-phase voltage range 110V - 400V AC 50/60 Hz,  
neutral line is not needed

Max. current per supply: 3 x 16A

Type of cable: H07RN-F 5G2.5 mm<sup>2</sup>

Cable length: 3 m

1st cable end: CEE-plug 16A / 400V (IEC309, red)

2nd cable end: Wago plug