

# Rittal – The System.

Faster – better – everywhere.



## TX 7888.721

## Network rack TX CableNet

State: 01/05/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TX 7888.721 - Network rack TX CableNet with glazed door

The TX CableNet – places extra space at your disposal by avoiding the problem of unnecessarily wide or deep IT racks. This IT network rack is thus also suitable for use in smaller IT environments and is already optimally prepared for individual interior installation.



## Features

|                     |  |
|---------------------|--|
| Model No.           | TX 7888.721  |
| Design              | 2nd generation<br>may be dismantled<br>with glazed door<br>with side panels<br>With roof plate   |
| Product description | Optimum IT rack solution for use in tight spaces, in rooms with low ceilings or wherever accessibility is otherwise restricted. No power losses due to unused rack space in case of population with exclusively small electrical components.   |
| Benefits            | New roof plate concept: Optimised use of the entire enclosure volume with the enclosure cabling plus optional integration of a fan module<br>Efficient frame concept, in a dismantlable version, for individual configuration and optional dismantling as required.<br>Side panels, screw-fastened for rapid access<br>482.6 mm (19") mounting angles, variable in the width and depth, with possibility for asymmetrical interior installation<br>Dismantling options |

# Features

|                                      |   |
|--------------------------------------|---|
| Material                             | Enclosure: Sheet steel<br>Door: Sheet steel, 1.2 mm<br>Side panel: Sheet steel, 1.2 mm<br>482.6 mm (19") mounting angles: Sheet steel, 2 mm<br>Side panel: Sheet steel, 1.2 mm  |
| Surface finish                       | Enclosure frame: Dipcoat-primed<br>Enclosure panels: Dipcoat-primed, powder-coated  |
| General colour                       | RAL 7035  |
| Colour                               | RAL 7035  |
| Supply includes                      | Enclosure with glazed front door and rear door<br>Enclosure frame, dismantlable, with 482.6 mm (19") mounting angles, front and rear<br>Side panels<br>Screw-fastened roof plate with concealed cable entry on both sides across the entire enclosure depth plus a central, concealed cut-out for easy integration of a fan module. |
| Dimensions                           | Width: 800 mm<br>Height: 2,000 mm<br>Depth: 1,000 mm  |
| Units                                | 42 U  |
| Distance between levels as delivered | 645 mm  |
| 482.6 mm (19") attachment            | may be dismantled   |
| Design                               | with side panels  |
| Rear door design                     | Sheet steel door, one-piece, solid  |
| Front door design                    | Glazed door, one-piece<br>With 3 mm single-pane safety glass<br>Door opening angle when baying: max. 105°   |
| Load capacity                        | 5000 N  |
| Load capacity (static)               | 500 kg  |
| Protection category to IEC 60 529    | IP 20   |

# Features

---

|                       |   |
|-----------------------|---|
| Note                  | To install a fan module, brush strips for fitting to the cable shunting openings are necessary if these are being used, or if the covers have been removed.<br>Brush strips to conceal the cable entry are available separately and may be conveniently ordered from our accessory range. |
| Basic material        | Sheet steel   |
| Packs of              | 1 pc(s).  |
| Net weight            | 123.5 kg  |
| Gross weight          | 133.5 kg  |
| Customs tariff number | 94039910  |
| ETIM 9                | EC002499  |
| ETIM 8                | EC002499  |
| ECLASS 8.0            | 27180207  |
| Product description   | TX CableNet, with glazed door, with roof plate, side panels, 19" mounting angles, rack can be dismantled, WxHxD: 800x2000x1000 mm, RAL 7035   |

---

# Approvals

---

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |

---

# Tender text

IT rack, installation height 42 U, glazed door at the front, readily dismantled, One-piece closed sheet steel door at the rear. Article number 7888.721

## Frame structure:

IT rack, consisting of a torsion-resistant, welded (>,<) symmetrical frame made of rolled and 16-folded vertical profiles, connected to a horizontal frame below and horizontal cross profiles, with screwed roof plate at the top. All frame profiles, with integrated system perforation in a 25 mm hole grid, enable convenient interior design by simply hanging and securing the installation components. All profile edges are rounded. The vertical frame profiles each have two in depth and width staggered mounting levels, which can be individually adjusted for flexible fastening of the components. The baying of the cabinets is possible at the front, back and side. Load capacity: up to 500 kg.

## Floor:

Open floor frame, without floor panels, optionally for individual equipping with floor modules from the accessories range.

## Front and back door:

Transparent door at the front, with 3 mm toughened safety glass. Steel sheet door at the rear, one-piece, closed. Front and rear doors each double hinged, with designer handle and 2-point bar lock, Safety lock 3524 E, replaceable with AX comfort handle. Optional integration of a semi-cylinder. Swapping door hinge side possible, door opening angle 135° when installed individually, 105° in array. Door hinges with captive hinge pins.

## Roof sheet:

Sheet steel roof, one-piece, closed, screwed, cable routing on both sides across the entire depth of the cabinet, prepared in the middle for fan installation.

Roof plate can be rotated for cable routing at the front and rear. To support passive ventilation, the roof plate can optionally be raised using spacers.

## Mounting levels:

Cabinet pre-assembled with two 482.6 mm (19") mounting levels, front and rear. The total static load capacity of both assembly levels is 500 kg.

Mounting levels consisting of universal profile rails, front and rear, variable in width and depth, in 15 mm dimensions, on depth struts at the top and bottom

in the cabinet frame, screwed. The 19" mounting levels can't be positioned with offset inside the housing.

Profile rails at the front and back, included additional hole pattern according to standard EIA 310 E. All height units marked on the profile rails and numbered bidirectionally.

Unit marking on both mounting levels for simplified assembly of the installation components can be read from the front outside and the back inside. Profile rails at the front prepared for tool-free mounting of cable management aids for organizing structured cabling within highest packing density.

Profile rails at the rear prepared to accommodate a Power Distribution Unit (PDU) on both sides with the 1U form factor, without consumption of installation volume due to the special space-saving lateral installation between the mounting level and the side wall within Zero U Space.

Side walls:

One-piece screwed side walls mounted on the cabinet.

Material:

Cabinet frame, roof: sheet steel 1.5 mm

Roof cutouts: 1.2mm

Rear door: sheet steel 1.2 mm

Front door: sheet steel 1.2 mm, safety glass 3.0 mm

19" profile rails: sheet steel 2.0 mm

Surface:

Flat parts, doors dip-primed, powder-coated in RAL 7035

Interior installation dip primed in RAL 9005

Cabinet frame dip primed in RAL 7035

Approvals:

CE declaration of conformity

RoHS 3

Dimensions (WHD): 800x2000x1000 mm

Item number: 7888.721

Manufacturer: Rittal GmbH & Co. KG