

# Rittal – The System.

Faster – better – everywhere.



## DK 7480.300

## Energy-Box, 482.6 mm (19")

State: 13/04/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7480.300 - Energy-Box, 482.6 mm (19") Pull-out

Designed to accommodate both DC and AC components, pull-out component front for optimum access to the wiring space from above and below.

## Features

|                          |   |
|--------------------------|---|
| Model No.                | DK 7480.300   |
| Product description      | Depth-variable top hat rail for snap-in attachment of installed equipment to DIN 43 880 in sizes 1 – 3 (e.g. to accommodate flush-type socket outlets, circuit-breakers, etc. or entire installed assemblies). Cable clamping at the rear. Two power distribution rails with connection clamps on an insulated base/plinth. Plastic cover including extension cover. Maximum capacity = 22 HP (22 x 18 mm = 396 mm). Enclosure height: 3 U. Enclosure depth: 223 mm. Maximum extension: 220 mm. Connection clamps: 4 clamps 35 mm <sup>2</sup> , 18 clamps 16 mm <sup>2</sup> (per rail). |
| Colour                   | RAL 7035  |
| Supply includes          | Energy-Box with plastic blanking covers.<br>Connection clamp<br>18 connection clamps, 16 mm <sup>2</sup><br>4 connection clamps, 35 mm <sup>2</sup><br>Strain relief<br>Identification strips<br>Brush strip  |
| Max. pitch units @ 18 mm | 22  |
| Dimensions               | Width: 482.6 mm<br>Depth: 220 mm  |
| Units                    | 3 U   |
| Packs of                 | 1 pc(s).  |
| Net weight               | 6.1 kg  |
| Gross weight             | 6.14 kg   |
| Customs tariff number    | 94032080  |
| ETIM 9                   | EC002006  |

# Features

---

ECLASS 8.0

27189268

---

Product description

DK Energy-Box, 482.6 mm (19"), Pull-out

## Tender text

Energy box, 3 U, pull-out

This Energy-Box is designed to accommodate both DC and AC modules. The pull-out module front affords optimum access to the wiring space from above and below.

Technical specifications:

Depth-variable top-hat rail for "snap-in" attachment of installed equipment as per DIN 43880 in sizes 1 - 3.

Cable clamping at rear.

2 power distribution rails with connection clamps mounted on isolated plinths.

Plastic cover including extension covers.

18 pcs. connection clamps, 4 mm<sup>2</sup>

4 pcs. connection clamps, 16 mm<sup>2</sup>

Max. number of installed devices = 22 (width = 18 mm)

Depth = 220 mm