

**Rittal – The System.**

Faster – better – everywhere.



**VX 8100.745**

**Punched section without mounting  
flange, 23 x 64 mm**

State: 06/04/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8100.745 - Punched section without mounting flange, 23 x 64 mm for VX, VX SE

For variable, individual interior installation of the enclosure frame on the inner mounting level.



## Features

|                      |   |
|----------------------|---|
| Model No.            | VX 8100.745   |
| Product description  | For variable, individual interior installation of the enclosure frame on the inner mounting level. Mounted flush with enclosure frame The additional mounting brackets mean it can also be used with a pre-installed mounting plate, and is also prepared for cutting to any required length. |
| Benefits             | System punchings on all four sides<br>With slots at the top and bottom for cage nuts, for attaching your own components via metric screws   |
| Material             | Sheet steel   |
| Surface finish       | Zinc-plated   |
| Supply includes      | 2 punched sections without mounting flanges<br>4 mounting brackets<br>Assembly parts  |
| Installation options | In VX on the inner mounting level, on the VX enclosure section<br>In the VX SE, on the vertical enclosure section in conjunction with the VX adaptor rail<br>Between two punched sections on the inner mounting level   |

# Features

---

|                       |   |
|-----------------------|---|
| To fit                | Enclosure type: VX<br>VX SE<br>Width/depth: 1,200 mm                        |
| Packs of              | 2 pc(s).  |
| Net weight            | 2.4 kg  |
| Gross weight          | 2.82 kg   |
| Customs tariff number | 73269098  |
| ETIM 9                | EC002625  |
| ECLASS 8.0            | 27189234  |
| Product description   | VX punched section without mounting flange, 23 x 64 mm, for W/D:<br>1200 mm |

# Approvals

---

|              |                 |
|--------------|-----------------|
| Explanations | PCF-declaration |
|--------------|-----------------|