


Rittal – The System.

Faster – better – everywhere.



VX 8619.730

**Punched section with mounting
flange, 14 x 39 mm**

State: 28/04/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8619.730 - Punched section with mounting flange, 14 x 39 mm for VX, VX SE, PC, IW, AX

For securing cable ducts, cable conduit holders, equipment installed on the door, etc.



Features

Model No.	VX 8619.730
Product description	For attaching cable ducts, cable conduit holders, equipment installed on the door, etc.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Distance between fixing points	675 mm
To fit door width	800 mm
VX installation options	In door width 800 mm
VX SE installation options	In door width 800 mm
AX installation options	In enclosure height 800 mm, in conjunction with rail for interior installation AX
AX stainless steel installation options	In enclosure height 800 mm
Installation options, AX plastic	In door width 800 mm
PC installation options	In door width 800 mm

Features

CX installation options	In door width 800 mm
VX base/plinth installation options	In base/plinth width 850 mm for mounting on the base/plinth corner pieces
Assembly instruction	For installation in AX sheet steel, only in conjunction with rail for interior installation AX
Note	For installing your own components on the punched section with mounting flange, metal screws or self-tapping M5 screws are required
To fit	Enclosure type: VX VX SE PC AX AX plastic CX one-piece console CX pedestal Suitable for width or height or depth: 800 mm
To fit	Base/plinth system VX
Packs of	4 pc(s).
Net weight	1.4 kg
Gross weight	1.588 kg
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189234
Product description	VX Punched section, with mounting flange 14 x 39 mm, for door width: 800 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------