Rittal - The System.

Faster – better – everywhere.





VX 8620.062

Base/plinth corner pieces with base/plinth trim panels, front and rear, 200 mm, stainless steel

State: 06/11/2025 (Source: rittal.com/gr-en)

NCLOSURES

OWER DISTRIBUTION

LIMATE CONTROL

T INFRASTRUCTURI

SOFTWARE & SERVICES

VX 8620.062 - Base/plinth corner pieces with base/plinth trim panels, front and rear, 200 mm, stainless steel

Base/plinth corner pieces with moulded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point may be concealed with a corner and baying cover.

Features

Model No.	VX 8620.062
Product description	Base/plinth corner pieces with moulded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point may be concealed with a corner and baying cover.
Material	Base/plinth corner piece: Stainless steel 1.4301 (AISI 304) Base/plinth trim panel front/rear: Stainless steel 1.4301 (AISI 304) Corner and baying cover: Plastic
Surface finish	Trim panel: Brushed, grain size 400
Supply includes	4 base/plinth corner pieces 4 corner covers 1 baying cover 1 base/plinth trim panel, front/rear, 200 mm high 2 base/plinth trim panels, front/rear, 100 mm high Assembly parts
Note	Side base/plinth trim panels finish off a base/plinth unit or provide additional stabilisation between base/plinths or enable interior configuration of the base/plinth Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system
Dimensions	Height: 200 mm
To fit	Width: = 1,000 mm

© Rittal 2025 2

Features

Type rating to UL 50E	Type 1
	Type 3R
	Type 4
	Type 4X
	Type 12
Weight/pack	12.7 kg
Packs of	2 pc(s).
Net weight	8.96
Customs tariff number	94039910
EAN	4028177922358
ETIM 9	EC000721
ECLASS 8.0	27182003

Approvals

Approvals UL + C-UL - FTTA