


# Rittal – The System.

Faster – better – everywhere.



## VX 8617.210

# Punched section with mounting flange, 23 x 64 mm

State: 23/05/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8617.210 - Punched section with mounting flange, 23 x 64 mm for VX, VX IT, VX SE, AX plastic

For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures.



## Features

|                         |   |
|-------------------------|---|
| Model No.               | VX 8617.210   |
| Product description     | For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures.  |
| Benefits                | Simply locate into the system punchings and screw-fasten<br>System punchings on all four sides<br>With slots at the top and bottom for cage nuts, for attaching your own components via metric screws |
| Material                | Sheet steel   |
| Surface finish          | Zinc-plated   |
| Supply includes         | Assembly parts  |
| VX installation options | In enclosure height 2200 mm, on the inner mounting level  |
| To fit                  | Enclosure type: VX<br>VX IT<br>Suitable for width or height or depth: 2,200 mm  |
| Packs of                | 4 pc(s).  |
| Net weight              | 8.824 kg  |

# Features

---

|                               |   |
|-------------------------------|---|
| Gross weight                  | 9.56 kg   |
| PCF per pack (cradle-to-gate) | 49.46   |
| Customs tariff number         | 73269098  |
| ETIM 9                        | EC002620  |
| ECLASS 8.0                    | 27189234  |
| Product description           | VX Punched section, with mounting flange 23 x 64 mm, for inner mounting level |

# Approvals

---

|              |                 |
|--------------|-----------------|
| Explanations | PCF-declaration |
|--------------|-----------------|