

Rittal – The System.

Faster – better – everywhere.



VX 8620.072

Base/plinth trim panels, side, 100 mm, stainless steel

State: 13/05/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8620.072 - Base/plinth trim panels, side, 100 mm, stainless steel for base/plinth system VX

Stainless steel base/plinth trim panels are used in the depth to finish off a base/plinth unit at the sides or for the interior installation of bayed base/plinths. The 100 mm high trim panels may also be used in a 200 mm high base/plinth and combined.

Features

| | |
|-----------------------|--|
| Model No. | VX 8620.072 |
| Product description | To finish off a base/plinth unit at the sides and for additional stabilisation or for the interior configuration of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths. |
| Material | Stainless steel 1.4301 (AISI 304) |
| Surface finish | Brushed, grain 400 |
| Supply includes | Assembly parts |
| Note | Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system |
| Dimensions | Height: 100 mm |
| To fit | Depth: = 600 mm |
| Type rating to UL 50E | Type 1 Type 3R Type 4 Type 4X Type 12 |
| Weight/pack | 2.8 kg |
| Packs of | 2 pc(s). |
| Net weight | 1.72 kg |
| Gross weight | 1.82 kg |
| Customs tariff number | 94039910 |

Features

| | |
|---------------------|--|
| ETIM 9 | EC000721 |
| ECLASS 8.0 | 27182003 |
| Product description | VX Base/plinth trim panel, side, H: 100 mm, for D: 600 mm, stainless steel, 1.4301 |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|
