

# Rittal – The System.

Faster – better – everywhere.



## SV 9345.734

### Circuit-breaker component adaptor

State: 12/01/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9345.734 - Circuit-breaker component adaptor 4-pole

## Features

Model No.	SV 9345.734
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Supply includes	Copper spacer roll Connection screws
Rated current max.	500 A
Rated operating voltage	690 V, 4~
Cable outlet	Bottom
For bar systems with centre-to-centre spacing	60 mm
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgear The technical data may vary for UL applications
Number of poles	4-pole
Dimensions	Width: 185 mm Height: 300 mm
To fit busbars	Height: 5, 10 mm
To fit manufacturer (model)	Siemens
To fit manufacturer (model)	Siemens (VL400)
Packs of	1 pc(s).
Net weight	3.36
Gross weight	3.489
Copper weight (kg per piece)	2.103
Customs tariff number	85369095
EAN	4028177684546

# Features

---

ETIM 9 EC001531

---

ECLASS 8.0 27370304

# Approvals

---

Explanations Declaration of conformity