

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.612

## RiLineX CB component adaptor

State: 13/05/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.612 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.



## Features

|                                      |   |
|--------------------------------------|---|
| Model No.                            | RX 9360.612   |
| Design                               | universal   |
| Benefits                             | Direct mounting of moulded-case circuit-breakers (MCCBs) on the board<br>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm<br>Fast, simple pre-assembly of standard market switch types outside of the enclosure |
| Material                             | Polyamide (PA 6)<br>Fire protection corresponding to UL 94  |
| Colour                               | RAL 9005<br>RAL 35745   |
| Supply includes                      | 3 connection space covers   |
| IP protection category to IEC 60 529 | IP 2XB  |
| Rated impulse withstand voltage Uimp | 8 kV  |

# Features

|                                   |   |
|-----------------------------------|---|
| Rated voltage                     | 690 V AC<br>690 V DC<br>600 V AC (UL)   |
| Rated insulation voltage $U_i$    | 1,000 V   |
| Contamination level               | 3   |
| Number of poles                   | 3-pole  |
| Cable outlet                      | Bottom  |
| Cross-section                     | 15 mm <sup>2</sup><br>6 mm <sup>2</sup>   |
| To fit manufacturer (model)       | Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor. |
| To fit busbar system              | RiLineX<br>RiLine60   |
| Fundamental frequency             | 50...60 Hz  |
| Ambient humidity (non-condensing) | 10...90 %   |
| To fit busbars                    | 15 x 5/10<br>20 x 5/10<br>30 x 5/10   |
| Operating temperature range       | -25 °C...55 °C  |
| Storage temperature range         | -25 °C...75 °C  |
| Dimensions                        | Width: 108.7 mm<br>Height: 251.4 mm<br>Depth: 62.8 mm   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 1.472 kg  |
| Gross weight                      | 1.474 kg  |
| Copper weight (kg per piece)      | 0.608   |
| Customs tariff number             | 85369095  |
| ETIM 9                            | EC001531  |

# Features

---

|                     |  |
|---------------------|--|
| Product description | RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting. Version for cable outlet at the bottom. |
|---------------------|--|

# Approvals

---

|              |  |
|--------------|--|
| Approvals    | UL + C-UL (listed)                           |
| Explanations | Declaration of conformity<br>PCF-declaration |

# Tender text

## RiLineX CB component adaptor (Universal Fix)

RiLineX CB component adaptor  
for 60 mm busbar systems.

Fastening is carried out using u-nuts in  
the two adjustable support rails.

For voltages up to 690 V AC and 690 V DC.

IEC and UL approved.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm x 5/10 mm

Rated current: 250 A

Connection: 90 mm<sup>2</sup>

Cable outlet: bottom

Dimensions: 108 mm x 251 mm x 51 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9360612