Rittal – The System.

Faster – better – everywhere.





KEL 9303.000 Ex enclosures

State: 08/12/2025 (Source: rittal.com/gr-en)



KEL 9303.000 - Ex enclosures stainless steel, empty enclosure with screw-fastened cover

Ex enclosure with screw-fastened cover, stainless steel







Features

Model No.	KEL 9303.000
Design	Ex enclosures
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EC
	Ambient temperature range: -30 °C+80 °C
	The specified temperatures may be limited by the installed equipment
	Explosion protection category to EN 60 079: Equipment protection
	thanks to increased safety (Ex e), equipment protection thanks to
	enclosure (Ex tb)
Material	Enclosure: Stainless steel 1.4301 (AISI 304)
	Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in
	silicone seal
Surface finish	Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 μm
Supply includes	Enclosure
	Cover
Dimensions	Width: 200 mm
	Height: 200 mm
	Depth: 80 mm

© Rittal 2025

Features

Certificate IEC EX PTB 09.0033U	Yes
Certificate PTB 03 ATEX 1013U	Yes
Basic material	Stainless steel 1.4301 (AISI 304)
IP protection category to IEC 60 529	IP 66
Packs of	1 pc(s).
Net weight	1.9
Gross weight	2.04
Customs tariff number	94032080
EAN	4028177138582
ETIM 9	EC002503
ECLASS 8.0	27180502

Approvals

Approvals	ATEX
	ATEX QA
	CQC-CCC
	IECEx
	IECEx QAR
Explanations	Attestation of Conformity

© Rittal 2025 3