

# Rittal – The System.

Faster – better – everywhere.



## RX 9362.035

# RiLineX NH fuse-switch disconnecter

State: 21/05/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9362.035 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 00 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 1.5 to max. 95 mm<sup>2</sup>. Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.



## Features

|   |   |
|---|---|
| Model No.                                     | RX 9362.035   |
| Design  | For 60 mm busbar systems  |
| Benefits                                      | Cover: can be locked and prepared for a lead seal<br>Voltage test through separate opening<br>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm<br>Tool-free changeover of the cable outlet<br>Park position for simpler maintenance work<br>All variants also available with electronic fuse monitoring |
| Material                                      | Polyamide (PA 6)<br>Fire protection corresponding to UL 94<br>Contact tracks: Electrolytic copper, silver-plated  |
| Colour  | RAL 9005<br>RAL 35745   |
| Supply includes                               | Connectors for electronic fuse monitoring   |
| For bar systems with centre-to-centre spacing | 60 mm   |
| Cable outlet                                  | Top/bottom  |

# Features

|  |  |
|--|--|
| Type of electrical connection                                      | Box terminal   |
| Fuse inserts   | NH 00<br>NH 000  |
| Rated insulation voltage $U_i$                                     | 1,000 V  |
| Rated operating voltage  | 690 V AC   |
| For NH size  | 00   |
| Test specification   | IEC/DIN EN 60 947-3<br>DIN EN 60 269-2 (fuse inserts)  |
| Dimensions   | Width: 106 mm<br>Height: 229.5 mm<br>Depth: 104.5 mm   |
| Operating temperature range  | -5 °C...35 °C  |
| Storage temperature range  | -25 °C...70 °C   |
| To fit busbars   | 15 x 5/10<br>20 x 5/10<br>30 x 5/10  |
| To fit busbar system   | RiLineX<br>RiLine60  |
| Number of poles  | 3-pole   |
| Utilisation category   | AC-23B (400 V/100 A)<br>AC-22B (500 V/100 A)<br>AC-21B (690 V/100 A)<br>DC-22B (250 V/100 A) |
| Contamination level  | 3  |
| with electronic fuse monitoring                                    | Yes  |
| IP protection category to IEC 60 529                               | IP 2XB   |
| Fire load  | 16.6 MJ/m <sup>2</sup>   |
| Connection of round conductors, fine wire without wire end ferrule | 1.5 - 95 mm <sup>2</sup>   |

# Features

|   |   |
|---|---|
| Connection of round conductors, fine wire with wire end ferrule | 1.5 - 95 mm <sup>2</sup>  |
| Heat loss max.  | 22 W  |
| Heat loss per fuse insert (max.)                                | 12 W  |
| Packs of  | 1 pc(s).  |
| Net weight  | 1.155 kg  |
| Gross weight  | 1.175 kg  |
| Copper weight (kg per piece)                                    | 0.409   |
| PCF per pack (cradle-to-gate)                                   | 7.86  |
| Customs tariff number   | 85369095  |
| ETIM 9  | EC001040  |
| Product description   | RiLineX NH fuse-switch disconnecter in size 00 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 1.5 to max. 95 mm <sup>2</sup> . Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring. |

# Approvals

|              |  |
|--------------|--|
| Approvals    | CQC-CCC                                      |
| Explanations | Declaration of conformity<br>PCF-declaration |