

Rittal – The System.

Faster – better – everywhere.



SV 9340.700 OM adaptors

State: 11/09/2025 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.700 - OM adaptors with connection cables

Features

Model No.	SV 9340.700
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Connection cables (AWG)	AWG 6
Rated current max.	65 A
Rated operating voltage	690 V, 3~
Electrical ratings UL (SCCR)	30 kA - 600 V, Fuse Class K5 max. 60 A, JDDZ/7 30 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7 65 kA - 600 V, Fuse Class J max. 60 A, JDDZ/7 65 kA - 480 V, Manual Motor Controller max. 63 A, NLRV/7 65 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7
For bar systems with centre-to-centre spacing	60 mm
Length of connection cable	130 mm
Support rail type	without support frame, 1 x 7.5 x 35 mm
Note	The technical data may vary for UL applications
Number of poles	3-pole
Dimensions	Width: 75 mm Height: 208 mm
Support rails Qty/height	1 / 7.5 mm
To fit busbars	Height: 5, 10 mm
Packs of	1 pc(s).
Net weight	0.259
Gross weight	0.42
Copper weight (kg per piece)	0.116

Features

Customs tariff number	85369095
EAN	4028177525566
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

OM adaptor 75 A
OM adaptor 75 A with connection cable, 3-pole,
for busbar thickness 5/10 mm and PLS 800/1600
Technical specifications
Connection cable: AWG 6 / approx. 16 qmm
Construction width: 75 mm
Length: 208 mm
Support frame: -mm
Support frame support: -
Insert strips: -
Support rail: 2
System:
Rittal RiLine60