


# Rittal – The System.

Faster – better – everywhere.



## RX 9364.022

## RiLineX bus-mounting fuse base

State: 11/10/2025 (Source: [rittal.com/gr-en](https://www.rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9364.022 - RiLineX bus-mounting fuse base

Compact RiLineX bus-mounting fuse base for 60 mm busbar systems. For cylinder lock 10 x 38 mm with optical LED fuse monitoring. For reliable contacting of the cylindrical fuses, the device features special fuse holders which are lockable in the open state and sealable in the closed state. Spring terminal blocks up to 16 mm<sup>2</sup> at an angle of 45° enable easier conductor connection. The device is suitable for tool-free snap-on mounting with semi-automatic busbar adjustment for 5 and 10 mm.



## Features

Model No.	RX 9364.022
Benefits	Reliable contacting of fuse inserts (without screw caps) Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm <sup>2</sup> Complete contact hazard protection without any additional accessories (such as screw caps)
Material	Polyamide (PA 6) Fire protection corresponding to UL 94-V0
Colour	RAL 35745 RAL 9005
Cable outlet	Bottom
Number of poles	3-pole
To fit busbar system	RiLineX RiLine60

# Features

Dimensions	Width: 18 mm Height: 263 mm Depth: 123.5 mm
Connection of round conductors, fine wire with wire end ferrule	1.5 - 6 mm <sup>2</sup>
Connection of round conductors, fine wire with AWG wire end ferrule	AWG 16 - AWG 10
Connection of round conductors, multi-wire	1.5 - 6 mm <sup>2</sup>
Connection of round conductors, multi-wire mm <sup>2</sup>	AWG 16 - AWG 10
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	400 V AC
Overvoltage category	4
Contamination level	3
Standards	IEC/DIN EN 60 947-3
Rated insulation voltage	800 V
Power dissipation (max.)	3 W
IP protection category to IEC 60 529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Utilisation category	AC-20B (400 V/100 A)
Fuse inserts	10 x 38 mm
Packs of	4 pc(s).

# Features

Net weight	1.008
Gross weight	1.014
Copper weight (kg per piece)	0.043
Customs tariff number	85369095
ETIM 9	EC001644

# Approvals

Explanations	Declaration of conformity
--------------	---------------------------