

**Rittal – The System.**

Faster – better – everywhere.



PK 9510.100

## Polycarbonate enclosures PK

State: 17/07/2025 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9510.100 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



## Features

|                                   |  |
|-----------------------------------|--|
| Model No.                         | PK 9510.100  |
| Design                            | Transparent cover  |
| Product description               | Use within the ambient temperature range: -35 °C...+80 °C. The specified temperatures may be limited by the installed equipment.   |
| Material                          | Enclosure: Fibreglass-reinforced polycarbonate<br>Cover transparent: Polycarbonate, all-round foamed-in PU seal<br>Cover screws: Polyamide<br>Insulating bungs: Polyethylene |
| Colour                            | RAL 7035   |
| Supply includes                   | Enclosure with cover<br>Cover screws<br>Insulating bungs for wall mounting screws  |
| Protection category NEMA          | NEMA 4X  |
| Protection category to IEC 60 529 | IP 66  |
| IK Code                           | IK08   |

# Features

|                             |   |
|-----------------------------|---|
| Dimensions                  | Width: 130 mm<br>Height: 130 mm<br>Depth: 75 mm |
| Operating temperature range | -35 °C...80 °C                                  |
| Basic material              | Polycarbonate                                   |
| Packs of                    | 4 pc(s).  |
| Net weight                  | 1.06  |
| Gross weight                | 1.26  |
| Customs tariff number       | 94037000  |
| EAN                         | 4028177139350                                   |
| ETIM 9                      | EC000261  |
| ECLASS 8.0                  | 27180101  |

# Approvals

|           |            |
|-----------|------------|
| Approvals | C-UL<br>UL |
|-----------|------------|