

Rittal – The System.

Faster – better – everywhere.



SV 9344.130

NH fuse-switch disconnector

State: 12/02/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.130 - NH fuse-switch disconnector with electronic fuse monitoring

Features

Model No.	SV 9344.130
Design	For mounting plate assembly with electronic fuse monitoring
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars for mounting plate assembly	Clamping area width: 32 mm Clamping area height: 10 mm
Cable outlet	Top/bottom
Type of electrical connection	Screw M10
Rated operating current max.	250 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	1
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 184 mm Height: 298 mm
Connection of round conductors	10 - 150 mm ²
Number of poles with electronic fuse monitoring	3-pole
Round conductor cross-section	10 - 150 mm ²

Features

Packs of	1 pc(s).
Net weight	2.3
Gross weight	2.343
Copper weight (kg per piece)	0.3
Customs tariff number	85365080
EAN	4028177540620
ETIM 9	EC000249
ECLASS 8.0	27371401

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK
