


# Rittal – The System.

Faster – better – everywhere.



## SV 9344.330

## NH fuse-switch-disconnectors, size 00 to 3

State: 17/06/2025 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9344.330 - NH fuse-switch-disconnectors, size 00 to 3 with electronic fuse monitoring

## Features

Model No.	SV 9344.330
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars	Clamping area width: 50 mm Clamping area height: 10 mm
for mounting plate assembly	Yes
Cable outlet	Top/bottom
Type of electrical connection	Screw M10
Rated operating current max.	630 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	3
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 250 mm Height: 298 mm
Connection of round conductors	10 - 300 mm <sup>2</sup>
Number of poles	3-pole
Packs of	1 pc(s).
Net weight	4.4
Gross weight	4.444
Copper weight (kg per piece)	1.06

# Features

Customs tariff number	85369095
EAN	4028177542051
ETIM 9	EC000249
ECLASS 8.0	27371401

# Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK