


Rittal – The System.

Faster – better – everywhere.



RX 9360.625

State: 19/07/2025 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.625 -

CB component adaptor (3-pole, max. 400 A) for the RiLineX busbar platform and 60 mm busbar systems such as RiLine60. The device width on the busbar system is 140 mm. The universal variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free, snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. The cable outlet is easily converted to the top or bottom to suit individual requirements.

Features

| | |
|--------------------------------------|---|
| Model No. | RX 9360.625 |
| Design | universal |
| Benefits | Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Tool-free changeover of the cable outlet Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure High rated voltage 800 V ready |
| Material | Polyamide (PA 6) Fire protection corresponding to UL 94 |
| Colour | RAL 9005 RAL 35745 |
| Supply includes | Including 3 connection space covers, 2 cross members and assembly parts |
| IP protection category to IEC 60529 | IP 2XB |
| Rated current max. | 400 A |
| Rated current (UL) | 400 A |
| Rated impulse withstand voltage Uimp | 12 kV |
| Rated voltage | 690 V AC 690 V DC 600 V AC (UL) |

Features

| | |
|-----------------------------------|-------------------------------------|
| Rated insulation voltage | 1,000 V |
| Rated impulse withstand current | 80 mA |
| Overvoltage category | 4 |
| Contamination level | 3 |
| Number of poles | 3-pole |
| Cable outlet | Top/bottom |
| Type of electrical connection | Screw M10 |
| To fit busbar system | RiLineX RiLine60 |
| Fundamental frequency | 50...60 Hz |
| Ambient humidity (non-condensing) | 10...90 % |
| To fit busbars | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Operating temperature range | -25 °C...55 °C |
| Storage temperature range | -25 °C...75 °C |
| Dimensions | Width: 140 mm Height: 325 mm |
| Packs of | 1 pc(s). |
| Net weight | 3.6 |
| Gross weight | 3.8 |
| Copper weight (kg per piece) | 1.652 |
| Customs tariff number | 85369095 |
| EAN | 4028177997073 |
| ETIM 9 | EC001531 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |