

Rittal – The System.

Faster – better – everywhere.



RX 9362.350

RiLineX Fuse-switch disconnecter

State: 19/07/2025 (Source: [rittal.com/gr-en](https://www.rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9362.350 - RiLineX Fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 3 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 120 to max. 300 mm². Cable outlet can be at the top or bottom, as required.

Features

| | |
|---|---|
| Model No. | RX 9362.350 |
| Benefits | Cover: can be locked and prepared for a lead seal Voltage test through separate opening Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Tool-free changeover of the cable outlet Park position for simpler maintenance work High rated voltage 800 V ready All variants also available with electronic fuse monitoring |
| Material | Polyamide (PA 6) Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated |
| Colour | RAL 9005 RAL 35745 |
| For bar systems with centre-to-centre spacing | 60 mm |
| Cable outlet | Top/bottom |
| Type of electrical connection | Box terminal |
| Rated operating current max. | 630 A |
| Rated operating voltage | 690 V AC |
| For NH size | 3 |
| Test specification | IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts) |

Features

| | |
|--------------------------------------|--|
| Dimensions | Width: 250 mm Height: 299 mm Depth: 135 mm |
| Operating temperature range | -5 °C...35 °C |
| Storage temperature range | -25 °C...70 °C |
| To fit busbars | 15 x 5/10 20 x 5/10 30 x 5/10 |
| To fit busbar system | RiLineX RiLine60 |
| Number of poles | 3-pole |
| Contamination level | 3 |
| IP protection category to IEC 60 529 | IP 2XB |
| Power dissipation (max.) | 101 W |
| Packs of | 1 pc(s). |
| Net weight | 4.7 |
| Gross weight | 4.9 |
| Copper weight (kg per piece) | 2.255 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001040 |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|