
Rittal – The System.

Faster – better – everywhere.





SV 9690.040 Energy storage enclosure

State: 08/12/2025 (Source: rittal.com/gr-en)



SV 9690.040 - Energy storage enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. With flexible interior fit-out. Ideal for efficient and modular energy storage installation with slide rails.

Features

Model No.	SV 9690.040
Design	With flexible interior fit-out
Material	Enclosure frame: Sheet steel, 1.5 mm
	Roof plate: Sheet steel, 1.5 mm
	Door: Sheet steel, 1.5 mm
	Rear panel: Sheet steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed
	Door, roof and rear panel: Powder-coated, textured paint
Colour	RAL 7035
Supply includes	Enclosure frame
	Door and rear panel, perforated
	Roof plate
	Lock: 3 mm double-bit
Protection category to IEC 60 529	IP 20
Dimensions	Width: 600 mm
	Height: 2,000 mm
	Depth: 600 mm
Packs of	1 pc(s).
Net weight	66
Gross weight	66.2
PCF per pack (cradle-to-gate)	208.2 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight approximately calculated and self-declared
EAN	4028177044272
ETIM 9	EC000261

© Rittal 2025 2

Approvals

Explanations

Declaration of conformity

© Rittal 2025 3