Rittal – The System.

Faster – better – everywhere.





PK 9514.100 Polycarbonate enclosures PK

State: 09/12/2025 (Source: rittal.com/gr-en)



PK 9514.100 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.







Features

Model No.	PK 9514.100
Design	PK enclosure with transparent cover
Product description	Use within the ambient temperature range: -35 °C+80 °C. The specified temperatures may be limited by the installed equipment.
Material	Enclosure: Fibreglass-reinforced polycarbonate
	Cover transparent: Polycarbonate, all-round foamed-in PU seal
	Cover screws: Polyamide
	Insulating bungs: Polyethylene
Colour	RAL 7035
Supply includes	Enclosure with cover
	Cover screws
	Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08

© Rittal 2025

Features

Dimensions	Width: 180 mm
	Height: 110 mm
	Depth: 90 mm
Operating temperature range	-35 °C80 °C
Basic material	Polycarbonate
Packs of	2 pc(s).
Net weight	0.756
Gross weight	0.856
Customs tariff number	94037000
EAN	4028177139510
ETIM 9	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	C-UL
	DNV-GL
	UL
Explanations	Declaration of conformity

Tender text

Polycarbonate Housings without knockouts

Polycarbonate enclosure, transparent cover without knockouts

Enclosure: Fibreglass-reinforced polycarbonate

without knockouts for cable entry

Cover: Fibreglass-reinforced polycarbonate

all-round foamed-in PU seal Cover screws: Polyamide

© Rittal 2025 3

Insulating bungs: Polyethylene Supply includes: Cover screws

Insulating bungs for wall mounting screws

Accessories: Wall mounting bracket Protection category to IEC 60 529: IP 66 Protection category NEMA: NEMA 4X

Colour: similar to RAL 7035

Dimensions (W x H x T): 180 x 110 x 90 mm

© Rittal 2025 4