Rittal - The System.

Faster – better – everywhere.





SV 9677.265 NH slimline switch-disconnector

State: 07/12/2025 (Source: rittal.com/gr-en)



SV 9677.265 - NH slimline switch-disconnector

3-pole, for bar systems with 185 mm centre-to-centre spacing.

Features

Model No.	SV 9677.265
Design	3-pole, switchable
Function principle	Automatic quick-break contact allows operator-independent switching Double-break for reliable disconnection of the contacts
Material	Polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Partially silver-plated hard copper
Colour	Chassis: RAL 7035 Cover: RAL 7001 Handle: RAL 7016
For NH size	2
For bar systems with centre-to- centre spacing	185 mm
Cable outlet	Тор
Type of electrical connection	Screw M12
Installation type	Screw attachment
Number of poles	3-pole
Rated operating voltage	690 V (AC), 3~
Rated operating current max.	400 A
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 100 mm Height: 772 mm
Connection of round conductors	6 - 240 mm²
To fit busbars	Height: 10 mm

© Rittal 2025

Features

Packs of	1 pc(s).
Net weight	13.5
Gross weight	14
Copper weight (kg per piece)	4.003
Customs tariff number	85043129
EAN	4028177806788
ETIM 9	EC001040
ECLASS 8.0	27371401

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3