# Rittal – The System.

Faster – better – everywhere.





KX 1579.000 E-Box KX, sheet steel

State: 15.12.2025. (Source: rittal.com/hr-hr)



# KX 1579.000 - E-Box KX, sheet steel

The small enclosure KX, E-Box KX (sheet steel), offers remarkable ease of assembly and flexibility when selecting lock systems.







#### **Features**

KX 1579.000
The small enclosure KX, E-Box KX (sheet steel), offers remarkable ease of assembly and flexibility when selecting lock systems.
Enclosure: Sheet steel
Door: Sheet steel, all-round foamed-in PU seal
Enclosure and door: Dipcoat primed, powder-coated on the outside
textured paint
Mounting plate: Zinc-plated
RAL 7035
Enclosure with door
Mounting plate
Cam lock with 3 mm double-bit insert
180° hinge
NEMA 1
NEMA 3R
NEMA 4
NEMA 12
IP 66

© Rittal 2025

## **Features**

Type rating to UL 50E Type 1 Type 3R	
• •	
Type 4	
Type 12	
IK Code IK08	
Dimensions Width: 300 mm	
Height: 800 mm	
Depth: 155 mm	
Dimensions mounting plate (W x 275 mm x 785 mm	
H)	
Material thickness - enclosure 1,25 mm	
Material thickness - door 1,25 mm	
Material thickness of mounting 2 mm plate	
Nate	
Lock Number of locks: 2	
Lock Number of locks: 2	
Lock Number of locks: 2  Basic material Sheet steel	
Lock Number of locks: 2  Basic material Sheet steel  Packs of 1 pc(s).	
Lock Number of locks: 2  Basic material Sheet steel  Packs of 1 pc(s).  Net weight 12.287	
Lock Number of locks: 2  Basic material Sheet steel  Packs of 1 pc(s).  Net weight 12.287  Gross weight 12.98	he product weight,
Lock  Number of locks: 2  Basic material  Packs of  1 pc(s).  Net weight  12.287  Gross weight  12.98  PCF per pack (cradle-to-gate)  Note on PCF category  Number of locks: 2  Sheet steel  1 pc(s).  12.287  Cross weight  12.98  PCF per pack (cradle-to-gate)  A1.4 kg CO2 eq (Cat B)  Note on PCF category  Category B: PCF value (cradle-to-gate) based on the steel ste	he product weight,
Lock  Number of locks: 2  Basic material  Sheet steel  Packs of  1 pc(s).  Net weight  12.287  Gross weight  12.98  PCF per pack (cradle-to-gate)  Value (cradle-to-gate)  Alignment of locks: 2  Sheet steel  1 pc(s).  Value (sheet steel)  1 pc(s).  Value (cradle-to-gate)  Category B: PCF value (cradle-to-gate) based on the approximately calculated and self-declared	he product weight,
Lock  Number of locks: 2  Basic material  Sheet steel  Packs of  1 pc(s).  Net weight  12.287  Gross weight  12.98  PCF per pack (cradle-to-gate)  Al.4 kg CO2 eq (Cat B)  Note on PCF category  Category B: PCF value (cradle-to-gate) based on the approximately calculated and self-declared  Customs tariff number  84879059	he product weight,
Lock  Number of locks: 2  Basic material  Sheet steel  Packs of  1 pc(s).  Net weight  12.287  Gross weight  12.98  PCF per pack (cradle-to-gate)  Note on PCF category  Category B: PCF value (cradle-to-gate) based on the approximately calculated and self-declared  Customs tariff number  84879059  EAN  4028177816657	he product weight,
Lock  Number of locks: 2  Basic material  Sheet steel  Packs of  1 pc(s).  Net weight  12.287  Gross weight  PCF per pack (cradle-to-gate)  Note on PCF category  Category B: PCF value (cradle-to-gate) based on the approximately calculated and self-declared  Customs tariff number  84879059  EAN  4028177816657  E-Number Sweden  E3465241	he product weight,

© Rittal 2025 3

## **Approvals**

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Certificates	Protection category
Explanations	Manufacturer's declaration
	Declaration of conformity
	Declaration of conformity UK
	PCF-declaration

#### Tender text

Enclosure (E-Box)

Enclosure with door:

with mounting plate.

Stable sheet steel design, body folded from a single piece and welded, with protection channel all-round door opening, rear panel with eyelets for wall mounting bracket, Door hinged on the right, with foamed-in PU seal, with PE conductor connection in the enclosure and via U-shaped bracket in the door, for quick and easy earthing, cam lock with 3 mm double-bit insert to DIN 43668.

QR code:

QR code printed on body, cover and rating plate for clear identification and easy retrieval of relevant product information and documentation, and for clear traceability of the individual parts.

Accessories: Top hat rail, wall mounting bracket, support rail, Mini-comfort handle, modular cable entry.

Material:

Enclosure, door: Sheet steel

Mounting plate: Sheet steel, zinc-plated

Enclosure and door surface finish:

© Rittal 2025

Triple surface treatment for optimum protection against corrosion and resistance to mineral oils, lubricants, machining emulsions and solvents:

Nanoceramic coating, electrophoretic dipcoat priming Powder-coated on the outside in textured RAL 7035.

Protection category to IEC 60 529: IP 66

Protection category to UL 508A: Type 4

Dimensions (W x H x D): 300x800x155 mm

© Rittal 2025 5