## Rittal – The System.

Faster - better - everywhere.







## SG 2372.102 - Signal pillar 3-way LED

Identify malfunctions and operating statuses in machines and automated processes immediately with Rittal's flexible range of signal pillars to suit all applications. If you only need three standard signal colours, the plug-and-play 3-way LED signal system is the ideal choice.

## **Features**

Model No.	SG 2372.102
Design	for wall/base mounting
Benefits	Complete, ready-to-connect solution Extremely long service life of the LEDs (max. 100,000 hours, therefore maintenance-free) Minimal assembly work and warehousing costs
Technical specifications	3-stage, red, yellow, green Transmission angle: 3 x 120°
Cable entry	Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm
Type of electrical connection	Screwless spring terminals
Light	LEDs
Dimensions	Height: 211.5 mm
Operating temperature range	-20 °C50 °C
Protection category to IEC 60 529	IP 65
Rated operating voltage	24 V
Thread	M12 x 1.5
Packs of	1 pc(s).
Net weight	0.25
Gross weight	0.309
Customs tariff number	85318070
EAN	4028177953765
ETIM 9	EC001042

© Rittal 2025 2

## **Features**

ETIM 8	EC001042	
ECLASS 8.0	27371230	

© Rittal 2025 3