Rittal – The System.

Faster – better – everywhere.





HD 2410.011 Cable gland HD

State: 14.11.2025. (Source: rittal.com/hr-hr)




HD 2410.011 - Cable gland HD

More compact design and the lock nut is included with the supply.







Features

Model No.	HD 2410.011
Design	Standard
Benefits	Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms.
	Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications	Manufacturer
	Clean room technology (e.g. pharmaceuticals)
	Biotechnology
	Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303)
	Seal: EPDM, compliant with FDA 21 CFR 177.2600
Supply includes	Lock nut
Dimensions	Thread: M16 x 1.5
For cable diameters	5 - 10 mm
Operating temperature range	-20 °C100 °C

© Rittal 2025

Features

IP protection category to IEC 60 529	IP69 / IPX8 (5 bar, 30 min)
Packs of	5 pc(s).
Net weight	0.1
Gross weight	0.2
Customs tariff number	73072980
EAN	4028177928718
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

Approvals

Approvals	UR + C-UR (recognized)
	VDE

© Rittal 2025 3