## Rittal – The System.

Faster – better – everywhere.





# SZ 2411.811 Cable gland, brass

State: 28.11.2025. (Source: rittal.com/hr-hr)



## SZ 2411.811 - Cable gland, brass

Integrated clamping membrane ensure safe tightening and cable-friendly strain relief.

#### **Features**

Model No.	SZ 2411.811
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage.  Clamping membranes for even tightening and strain relief to protect the cables
Material	Brass Seal: CR/NBR
Surface finish	Nickel-plated
IP protection category to IEC 60 529	IP 68 (5 bar, 30 min)
Dimensions	Height: 28 mm
Thread	M16 x 1.5
Thread length	7 mm
Min. cable diameter	5 mm
Max. cable diameter	10 mm
Operating temperature range	-40 °C100 °C
torque	9 Nm
Width across flats	20 mm
Dimensions	Thread: M16 x 1.5 Thread length: 7 mm
Type rating to UL 50E	Type 4X
Packs of	15 pc(s).
Net weight	0.3
Gross weight	0.451

© Rittal 2025

### **Features**

Customs tariff number	74198090
EAN	4028177810082
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

## **Approvals**

Approvals	UR + C-UR (recognized) VDE
Explanations	Declaration of conformity  Declaration of conformity UK

© Rittal 2025 3