

Rittal – The System.

Faster – better – everywhere.



SK 3140.140

Roof-mounted fan, roof vent

State: 28.06.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Features

Air throughput, unimpeded air flow (without filter mats)	At 50 Hz: 863 m ³ /h At 60 Hz: 942 m ³ /h
Rated operating voltage	380 V - 415 V, 3~, 50 Hz/60 Hz 400 V - 480 V, 3~, 60 Hz
Power consumption Pel	At 50 Hz: 98 W At 60 Hz: 130 W
Rated current max.	At 50 Hz: 0.17 A At 60 Hz: 0.2 A
Dimensions	Width: 400 mm Height: 133 mm Depth: 400 mm
Installation depth	34,6 mm
Mounting cut-out	Cut-out width: 258 mm Cut-out depth: 258 mm
IP protection category to IEC 60529	IP 21 without filter mat IP 54 including pleated filter
Protection category NEMA	NEMA 12
Note	A chopped-fibre filter filter may optionally be used to increase the protection category to IP 55 (see accessories). To improve energy efficiency and extend the service life of the devices, we recommend the use of thermostats or temperature displays
Service life of fans (L10, 40 °C)	At 50 Hz: 63,500 h At 60 Hz: 61,500 h
Operating temperature range	-20 °C...55 °C
Storage temperature range	-40 °C...70 °C
Noise level	At 50 Hz: 56 dB(A) At 60 Hz: 58 dB(A)
Packs of	1 pc(s).
Net weight	6 kg
Gross weight	6,02 kg
Customs tariff number	84145915

Features

ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716
Product description	SK Roof-mounted fan TopTherm, 863/942 m ³ /h, 400-460 V, 3~, 50/60 Hz, WHD: 400 x 133 x 400 mm

Approvals

Approvals	CSA IEC CB 30 - KC Korea TÜV-tested safety UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK
