

Rittal – The System.

Faster – better – everywhere.



SK 3181.125 Pleated filter

State: 28.06.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3181.125 - Pleated filter for fan-and-filter units, roof-mounted fans, cooling units and chillers

The high-quality pleated filter technology permits a significant increase in the volumetric air flow compared to conventional chopped-fibre filter mats. Cooling unit performance is improved and energy consumption is lower. The enhanced filtration properties also mean less dust in the enclosure or unit, and the resulting longer maintenance intervals reduce service costs significantly.



Features

Model No.	SK 3181.125
Design	for fan-and-filter units / outlet filters
Material	Pleated filter: Based on polyester, meltblown polycarbonate Absorber mat: 100% polyester
Colour	White
Note	Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
To fit Model No.	3239.3xx 3239.7xx
Dimensions	Width: 167 mm Height: 167 mm Depth: 21 mm
Dimensions of absorber mat	Width: 173 mm Height: 173 mm
IP protection category to IEC 60529	IP 55 in fan-and-filter units/outlet filters

Features

Note on Model No.	No suitable for use in EMC fan-and-filter units.
Packs of	5 pc(s).
Net weight	0.24
Gross weight	0.26
Customs tariff number	56039390
EAN	4028177969100
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

Approvals

Approvals	UR + C-UR (recognized)
-----------	------------------------