

# Rittal – The System.

Faster – better – everywhere.



## SK 3210.500

## Air-water heat exchangers

State: 18.08.2025. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3210.500 - Air-water heat exchangers roof-mounted

For mounting on the roof surface. Cooling output 1.87 kW – 4 kW. Protection category IP 55 as standard. Particularly suitable for use in harsh environments. Flexible water connection options.



## Features

Model No.	SK 3210.500
Design	Water-carrying parts, copper/brass (Cu/CuZn)
Product description	For use in harsh environments and temperature ranges up to +70 °C. The air/water heat exchanger is assembled on the roof of the enclosure using flexible water connection options.
Colour	RAL 7035
Supply includes	Fully wired ready for connection (plug-in terminal strip) Drilling template Sealing mat Assembly parts
Total cooling output	L 35 W 10 at 400 l/h: 4 kW
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Power consumption Pel	At 50 Hz: 100 W At 60 Hz: 120 W
Rated current max.	At 50 Hz: 0.44 A At 60 Hz: 0.5 A
Permissible operating pressure (p. max.)	1 - 10 bar

# Features

Type of electrical connection	Plug-in terminal strip
Duty cycle	100 %
Cooling medium	Water (see Internet for specifications)
Water inlet temperature	1 °C...30 °C
Water connections	½" connector sleeve G ¾" external thread
Temperature control	e-Comfort controller (factory setting +35 °C)
Operating temperature range	1 °C...70 °C
Dimensions	Width: 597 mm Height: 417 mm Depth: 475 mm
Protection category	IP 65 available on request
Pre-fuse	Miniature circuit-breaker/fuse: 4 A
Setting range	20 °C...55 °C
Protection category to IEC 60 529	IP 55
Packs of	1 pc(s).
Net weight	34.2
Gross weight	36
Customs tariff number	84158300
EAN	4028177429963
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

# Approvals

Approvals	CSA UR + C-UR (recognized)
-----------	-------------------------------

# Approvals

Explanations

Declaration of conformity

## Tender text

Rittal TopTherm air/water heat exchanger  
roof-mounted, 4000 W,  
comfort controller, 230 V, 50/60 Hz  
Roof-mounted air/water heat exchanger

For use in tough environments. Flexible water  
connection options.

Total cooling output L 35 W 10, 400l/h: 4 kW  
Rated operating voltage: 230 V, 50/60 Hz  
Refrigerant: Water (see specifications)  
Water-carrying parts: Cu/CuZn  
Dimensions [W x H x D]: 597 x 417 x 475 mm  
Ambient temperature range: 1°C to 70°C  
Setting range: 20°C to 55°C  
Water inlet temperature range: 1°C to 30°C  
Temperature control and monitoring: Comfort controller  
with two floating fault signal outlets and door limit  
switch connection (factory setting +35°C)  
Type of connection: Plug-in terminal strip  
Protection category to IEC 60 529: IP 55  
Weight: 25.5 kg  
Colour: RAL 7035