

Rittal – The System.

Faster – better – everywhere.



SK 3237.118 TopTherm filter fans

State: 23.05.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3237.118 - TopTherm filter fans

Complete fan unit for tool-free mounting on surfaces. Air throughput from 20 - 900 m³/h, standard protection category IP 54.

Features

| | |
|--|--|
| Model No. | SK 3237.118 |
| Design | wall-mounted |
| Product description | Fan-and-filter units with diagonal fan technology have superior pressure stability and ensure a more constant air throughput. The diagonal direction of outflow ensures more even heat dissipation from the enclosure. |
| Product modification | The cover for the connection clamp has not been part of the TopTherm filter fans since May 2024. In testing, it proved not to be necessary to meet the standard, and affects neither function nor operational reliability. |
| Colour | RAL 9005 |
| Supply includes | Complete unit ready to install, including chopped-fibre filter mat |
| Fan | Axial, shaded pole motor |
| Air throughput, unimpeded airflow (with chopped-fibre filter) | At 50 Hz: 20 m ³ /h At 60 Hz: 25 m ³ /h |
| Air throughput with outlet filter including chopped-fibre filter mat (quantity x order number) | 1 x 3237208: 15/18 m ³ /h 2 x 3237208: 16/20 m ³ /h |
| Rated operating voltage | 115 V, 1~, 50 Hz/60 Hz |
| Power consumption Pel | At 50 Hz: 11 W At 60 Hz: 9 W |
| Rated current max. | At 50 Hz: 0.12 A At 60 Hz: 0.13 A |
| Dimensions | Width: 116.5 mm Height: 116.5 mm |
| Installation depth | 43 mm |

Features

| | |
|-------------------------------------|---|
| Mounting cut-out | Cut-out width: 92 mm Cut-out height: 92 mm |
| IP protection category to IEC 60529 | IP 54 with chopped-fibre filter IP 56 with chopped-fibre filter and hose-proof hood |
| Protection category NEMA | Type 12 with chopped-fibre filter Type 3 Type 3R with chopped-fibre filter and hose-proof hood |
| Pre-fuse | Miniature circuit-breaker/fuse: 2 A |
| Note | To increase the air throughput, a pleated filter may optionally be used (see characteristic curve). Suitable for use with fan-and-filter units, roof-mounted fans and outlet filters. With the filter fan 3237.XXX, electrical connection is made via two single wires (length approx. 300 mm) on the unit, for all other filter fans, a screwless spring terminal is used |
| Service life of fans (L10, 40 °C) | At 50 Hz: 55,000 h At 60 Hz: 60,000 h |
| Operating temperature range | -15 °C...55 °C |
| Storage temperature range | -30 °C...70 °C |
| Noise level | At 50 Hz: 38 dB(A) At 60 Hz: 43 dB(A) |
| Packs of | 1 pc(s). |
| Net weight | 1,2 kg |
| Gross weight | 1,38 kg |
| Customs tariff number | 84145915 |
| ETIM 9 | EC000320 |
| ETIM 8 | EC000320 |
| ECLASS 8.0 | 27180716 |
| Product description | SK Fan-and-filter unit TopTherm, 20/25 m ³ /h, 115 V, 1~, 50/60 Hz, WHD: 116.5 x 116.5 x 16 mm |

Approvals

| | |
|--------------|---|
| Approvals | 30 - KC Korea UL + C-UL - FTTA UR + C-UR (recognized) |
| Explanations | Declaration of conformity Declaration of conformity UK |

Tender text

Fan-and-filter units with diagonal fan technology have superior pressure stability and ensure a more constant air throughput. The diagonal direction of outflow ensures more even heat dissipation from the enclosure

Air throughput (unimpeded air flow): 20 / 25 m³/h

Power consumption: 11 / 9 W

Rated current: 0,12 / 0,1 A

Rated operating voltage: 115 V, 1~, 50/60 Hz

Fan: Axial, shaded pole motor

Dimensions [WxH]: 116,5x116,5 mm

Build depth: 16 mm

Installation depth: 43 mm

Mounting cut-out [WxH]: 92x92 mm

Operating temperature range: -15°C to 55°C

Storage temperature range: -30°C to 70°C

Colour: RAL 9005

Protection category IP to IEC 60 529:

IP 54 with fleece filter

IP 56 with fleece filter and hose-proof hood

Protection category NEMA:

Type 12 with fleece filter

Type 3, 3R with fleece filter and hose-proof hood

Noise level: 38 / 43 db(A)

Service life of fans: 55.000 / 60.000 h

Weight: 0,48 kg